

metabo**Cordless hammer drill with Li-ion rechargeable battery BHLTX16****Order data**

Order number	075559 BHLTX16
GTIN	4061792191655
Item class	03D

Description**Version:****Power packs for hammer drilling.**

The hammer drill has a high-performance hammer action with a precise pneumatic impact mechanism that generates impacts with maximum impact energy with minimal pressure.

Hammer drill with 2 functions: **hammer drilling and drilling.**

- **Metabo VibraTech (MVT): health-friendly, low-fatigue working even in continuous use.**
- **Vario-Tacho-Constamatic (VTC) full-wave electronics for working with material-appropriate speeds that remain constant under load.**
- **Electronic safety shutdown of the motor when the tool is blocked for safe working.**
- **Very light, compact cordless hammer drill with brushless motor for low-fatigue drilling in any working position.**
- **Maximum drilling performance, efficiency and service life thanks to brushless technology and high-performance impact mechanism.**
- **LED work light provides a clear view of the bore area.**

Advantage:**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Includes 2x batteries, charger and MetaBOX.

With additional handle and depth stop.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Packaging	Metabox
maximum twist drill size Ø in wood	20 mm
No load speed	0 - 730 min ⁻¹
Impact energy	1.3 J
Battery capacity	2 Ah
Power supply	Mains operated
Weight without battery	1.6 kg
Type of rechargeable battery	Lithium-ion
Weight including rechargeable battery	2 kg
Manufacturer's designation	BH 18 LTX BL 16
Battery voltage	18 V
Tool arbor shape	SDS Plus
maximum twist drill size Ø in concrete	16 mm
maximum hammer rate	5250 min ⁻¹
Number of rechargeable batteries contained	2
maximum twist drill size Ø in steel	13 mm
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Type of product	Hammer drill