

**metabo****Cordless angle grinder with rechargeable battery, Type: WL9-125****Order data**

Order number	077127 WL9-125
GTIN	4061792225633
Item class	03D

**Description****Version:**

Robust 18 V angle grinder with powerful motor and slim design.

- **Metabo Quick for tool-free disc change using quick clamping nut.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Electronic safety shut-off function: reduces kick-back when the disc is blocked, providing excellent protection for the operator.**
- **Electronic soft start for smooth start-up.**
- **Restart protection: Prevents unintentional startup after battery change.**

**Advantage:**

**Batteries are 100% compatible – now also across different manufacturers.**

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

**Supplied with:**

Includes rechargeable battery, charger and metaBOX. Includes protective hood, support flange, quick clamping nut, additional handle and 3× Li-Power batteries.

**Note:**

See No. 073870 – 073890 for suitable batteries and chargers.

**Technical description**

Manufacturer's designation	W 18 L 9-125 Quick
----------------------------	--------------------

Number of rechargeable batteries contained	3
Weight without battery	1.6 kg
Restart block	yes
maximum disc Ø	125 mm
Weight	2.3 kg
Dead man's circuit	no
Packaging	Metabox
Soft start	yes
Type of rechargeable battery	Lithium-ion
Weight including rechargeable battery	2.3 kg
Kick-back stop	yes
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Battery capacity	4 Ah
Battery voltage	18 V
Power supply	Mains operated
maximum speed	8500 min <sup>-1</sup>
maximum vibration to EN	5 m/s <sup>2</sup>
Overload protection	yes
Type of product	Angle grinder

## Accessories

Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery charger Type ASC55	073890 ASC55