

metabo
Cordless angle grinder with rechargeable battery, Type: WVBLT11125

Order data

Order number	077127 WVBLT11125
GTIN	4061792206618
Item class	03D

Description
Version:

Speed-adjustable, brushless 18 V angle grinder with maximum efficiency.

- **Battery pack can be rotated in 90° increments.**
- **Fast braking system and safety shut-off.**
- **M-Quick system for tool-free disc change.**
- **Fast braking system for maximum user protection: Disc stops within 1 second after switching off.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked to the lowest level on the market – for maximum user protection.**
- **Electronic overload protection, soft start and restart protection.**
- **Removable dust filter to protect the motor from coarse particles.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Includes rechargeable battery, charger and metaBOX. Includes protective hood, support flange, M-Quick clamping nut, additional handle, dust protection filter and 2× LiHD batteries.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Soft start	yes
Dead man's circuit	no
Restart block	yes
maximum vibration to EN	8 m/s ²
Weight without battery	1.8 kg
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Motor design	brushless
Power supply	Mains operated
maximum speed	2800 - 10000 min ⁻¹
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Weight	2.8 kg
Kick-back stop	yes
Packaging	Metabox
Weight including rechargeable battery	2.8 kg
Manufacturer's designation	WVB 18 LT BL 11-125 Quick
Battery capacity	5.5 Ah
Battery voltage	18 V
Overload protection	yes
maximum cutting depth	27 mm
maximum disc Ø	125 mm
Type of product	Angle grinder

Accessories

Battery packLi-Power Battery capacity 4 A·h	073870 4
---	----------

Battery charger Type ASC55	073890 ASC55
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2