

metabo**Angle grinder, Type: W850-125****Order data**

Order number	077132 W850-125
GTIN	4007430338006
Item class	03D

Description**Version:****You set the limit – not your machine.**

With devices from 850 to 1,900 watts, you can find the right angle grinder for every requirement and application. **Handy compact angle grinder** for light work.

- **Powerful motor with good overload capability.**
- **Restart protection after power interruption.**
- **Robust, universal and economical: Powerful angle grinder for every application.**
- **Torsion-proof protective hood.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

Technical description

Power consumption	850 W
Connection thread	M14
maximum disc Ø	125 mm
Weight	1.8 kg
Cable length	2.5 m
Special features	Restart inhibit

Restart block	yes
Manufacturer's designation	W 850-125
Power supply	Mains-powered
No load speed	11500 min ⁻¹
Type of product	Angle grinder