

Garant**GARANT Softcut® HSI close pitch, with bore, Ø D / number of teeth Z: 40/5mm**

Order data

Order number	214908 40/5
GTIN	4045197674654
Item class	210

Description

Version:

Wear-resistant heat-treated steel with corrosion-inhibiting coating. Precise indexable insert seating by use of appropriate torque. Wide and close tooth pitches for individual milling strategies.

Application:

Particularly suitable for machines with lower drive power and for machining at greater depths and small entry diameters.

Note:

To use all **4 cutting edges**, the insert must **always be turned in the direction shown (anticlockwise)**.

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 8IP**.

For exact 90° corners, select $a_p = 6$ mm.

Technical description

maximum cutting depth $a_{p \max}$	6 mm
Cutting edge Ø D_c	40 mm
Mounting bore Ø	16 mm

Overall length L_{tot}	40 mm
suitable indexable insert	SO.. 0836..
Pack of insert screws	219863 (8IP; 2.2 Nm)
Number of cutting edges Z	5
Series	Softcut®
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Set of insert screws 10 pieces	219863
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2