

KERN**Platform scales, type DS high resolution, maximum weighing range: 36kg**

Order data

| | |
|--------------|---------------|
| Order number | 479611 36 |
| GTIN | 4045761357013 |
| Item class | 47D |

Description

Version:

- Robust platform scales can be used as parcel, industrial, and counting scales.
- Display unit with numeral height 21 mm can be remote from platform; can be stood or mounted using flexible cable.
- Robust platform with a protective hood over the display unit.
- Simple, self-explanatory user guidance with (yes/no) dialogue in the display.
- Selectable mains or battery operation (battery available on request).
- Units of weight (e. g. screw weight) can be freely programmed.
- With automatic reference optimisation for exact counting.
- Adjustment programme CAL: For accuracy adjustment (required calibration weight available on request).
- Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces.
- Display selectable between pieces and weight.
- Numeric tare preference for well-known container weight. Useful for filling quantities.
- Percentage determination: Display of deviation from the reference weight in % instead of in grammes.
- KERN Universal Port (KUP): allows the connection of external KUP interface adapters (not included) such as RS-232, USB for exchanging data and control commands, without installation effort.

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

Internal and external rechargeable battery, calibration weight, wall attachments, printer, stand and interface adapter such as RS-232, USB on request.

Technical description

| | |
|------------------------------|------------------|
| Minimum unit weight | 2 g |
| Reproducibility | 0.2 g |
| Settling time | 3 s |
| Net weight | 9.5 kg |
| Dimensions of weighing plate | 308×318 mm |
| Calibration | Price on request |
| maximum weighing range | 0 - 36 kg |
| Power supply | Mains operated |
| Manufacturer's designation | DS |
| Scale divisions | 0.2 g |
| Number height display unit | 18 mm |
| Type of product | Platform balance |

Services

| | |
|--|-----------|
| CalibrationScales maximum weighing range 50 kg | 027700 50 |
|--|-----------|