



Slotted reducing adapter with cooling, Ø 32 mm, Clamping Ø D1: 10mm



Order data

Order number	302177 10
GTIN	4060576155074
Item class	33T

Description

Version:

With cooling channel slots.

Application:

- **For drilling, reaming, milling, and tool sharpening.**
- **Very high flexibility due to reduction in clamping diameter.**
- **Very high torque guarantees a higher volume of metal removal compared to direct clamping.**
- **Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3 \times D$).**
- **Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).**
- **Can be used in all commercially available hydraulic clamping chucks.**

Suitable for:

Hydraulic clamping chuck **with clamping Ø 32 mm.**

Technical description

Overall length L	62.5 mm
Clamping Ø D ₁	10 mm
Ø D	32 mm
Product name attribute	Ø 32 mm
Concentricity system	5 μm
Type of product	Reducing adapter

