



Slotted reducing adapter with cooling, Ø 32 mm, Clamping Ø D1: 20mm



Order data

Order number	302177 20
GTIN	4060576155029
Item class	33T

Description

Version:

With cooling channel slots.

Application:

- For drilling, reaming, milling, and tool sharpening.
- Very high flexibility due to reduction in clamping diameter.
- Very high torque guarantees a higher volume of metal removal compared to direct clamping.
- Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3 \times D$).
- Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).
- Can be used in all commercially available hydraulic clamping chucks.

Suitable for:

Hydraulic clamping chuck with clamping Ø 32 mm.

Technical description

Ø D	32 mm
Overall length L	62.5 mm
Clamping Ø D ₁	20 mm
Product name attribute	Ø 32 mm
Concentricity system	5 μm
Type of product	Reducing adapter

