



## Slotted reducing adapter with cooling, Ø 32 mm, Clamping Ø D1: 25mm



### Order data

Order number	302177 25
GTIN	4060576155012
Item class	33T

### Description

#### Version:

With cooling channel slots.

#### Application:

- For drilling, reaming, milling, and tool sharpening.
- Very high flexibility due to reduction in clamping diameter.
- Very high torque guarantees a higher volume of metal removal compared to direct clamping.
- Concentricity  $\pm 5 \mu\text{m}$  (system accuracy at  $3 \times D$ ).
- Concentricity  $\pm 2 \mu\text{m}$  (for reducing adapter).
- Can be used in all commercially available hydraulic clamping chucks.

#### Suitable for:

Hydraulic clamping chuck with clamping Ø 32 mm.

### Technical description

Clamping Ø D <sub>1</sub>	25 mm
Overall length L	62.5 mm
Ø D	32 mm
Product name attribute	Ø 32 mm
Concentricity system	5 $\mu\text{m}$
Type of product	Reducing adapter

