



Digital dial indicator 0.01 mm reading, Measuring range: 12,5mm



Order data

Order number	434262 12,5
GTIN	7630041162578
Item class	45A

Description

Version:

Digital dial indicator with large LCD display. The dial rotates by 270° for optimal alignment of the measured value display for a variety of applications.

Function:

Zero setting/preset, measurement value output, reversible direction of measurement. Keypad lockable, standby mode.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Spare and special contact points No. 424900; 434910; 434915. Data cable No. 498928.

Technical description

Reversible reading	0.0005 in
Power supply	Battery-powered
Body Ø	59.8 mm
Calibration	C1

Number of batteries contained	1
Series	DIALTRONIC
Measuring range	0 - 12.5 mm
Battery type	Button cell
Gauging force	0.65 – 0.90 N
Article no of the battery / rechargeable battery fitted	081560 CR2032
Thickness of housing	33 mm
Clamping shank Ø h6	8 mm
Reversible reading	0.01 mm
Measurement variation E MPE (measurement range)	0.01 mm
Standard	DIN 878
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Preset function	yes
Measurement technology	digital
Type of product	dial gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023000 12,5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------