

**Digital dial indicator 0.001 mm reading, Measuring range: 12,5mm****Order data**

Order number	434263 12,5
GTIN	7630041152463
Item class	45A

**Description****Version:**

Digital dial indicator with large LCD display. The dial rotates by 270° for optimal alignment of the measured value display for a variety of applications.

**Function:**

Zero setting/preset, measurement value output, reversible direction of measurement. Keypad lockable, standby mode.

**Supplied with:**

1 battery No. 081560 size CR2032.

**Optional extras:**

Spare and special contact points No. 424900; 434910; 434915. Data cable No. 498928.

**Technical description**

Thickness of housing	33 mm
Calibration	C1
Reversible reading	0.00005 in
Reversible reading	0.001 mm

Body Ø	59.8 mm
Measuring range	0 - 12.5 mm
Series	DIALTRONIC
Gauging force	0.65 – 0.90 N
Number of batteries contained	1
Power supply	Battery-powered
Clamping shank Ø h6	8 mm
Battery type	Button cell
Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement variation E MPE (measurement range)	0.004 mm
Standard	DIN 878
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Preset function	yes
Measurement technology	digital
Type of product	dial gauge

## Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023000 12,5
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------