



## Digital dial indicator 0.001 mm reading, Measuring range: 25mm



### Order data

Order number	434291 25
GTIN	7630041152517
Item class	45A

### Description

#### Version:

Digital dial indicator with combined scale and digital display (10 mm character height) and mechanical tolerance marks. Display/button panel can be rotated up to 270°.

#### Function:

Zero setting/preset, measurement value output, reversible direction of measurement. Keypad lockable, standby mode. Definition of lower and upper tolerances, dynamic measurement Min/Max/Max-Min, selection Ref 1 or Ref 2 (preset and stored tolerance), multiplication factor, keyboard lock, data output, resolution selection (0.01 or 0.001 mm). IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

1 battery No. 081560 size CR2032.

#### Optional extras:

Data cable No. 498928, spare and special contact points No. 434900; 434910.

### Technical description

Battery type	Button cell
--------------	-------------

IP Index of Protection	IP 54
Measuring range	0 - 25 mm
Body Ø	59.8 mm
Reversible reading	0.001 mm
Calibration	C1
Clamping shank Ø h6	8 mm
Power supply	Battery-powered
Number of batteries contained	1
Series	DIALTRONIC
Reversible reading	0.00005 in
Article no of the battery / rechargeable battery fitted	081560 CR2032
Thickness of housing	33 mm
Gauging force	0.65 – 1.15 N
Measurement variation E MPE (measurement range)	0.004 mm
Standard	Works standard
Reversible reading	mm / inch
Height of numerals	10 mm
Interface	Digimatic interface
Interface	USB interface
Preset function	yes
Measurement technology	digital
Type of product	dial gauge

## Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100

## Accessories

Button cell / special battery Battery type CR2032

081560 CR2032