



Plug-in ratchet reversible, Type-Square drive: 1-1/4Fin



Order data

Order number	657600 1-1/4F
GTIN	4018754334735
Item class	63A

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Plug-in reversible ratchet.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

Technical description

Height h	13.8 mm
Long-term rated loading	42 Nm
Pitch S	17.5 mm
Series	735
Width b	24 mm
Square drive	1/4 in
Plug-in shank	9×12 mm
No. of teeth	60
Exchangeable tool	Plug-in head
Ratchet reversible	yes
Ratchet with ejector	no
Type of product	Ratchet