



Angle grinder Cordless, Type: 71220161



Order data

Order number	077107 71220161
GTIN	4014586898155
Item class	03F

Description

Version:

Dust-resistant and powerful 18V AMPShare cordless angle grinder for effective cutting, grinding and deburring work in assembly applications. Double the productivity – up to 50% more cuts than the previous system thanks to the perfect combination of a powerful machine and a powerful ProCORE battery system. Durable and robust thanks to completely closed motor housing. This protects the motor from aggressive ceramic and mineral dusts. Innovative cooling ribs ensure optimum cooling, including temperature monitoring.

- **Electronic speed pre-selection.**

Supplied with:

Without battery, without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

See No. 073863 – 073867 for a suitable starter set.

Technical description

Speed range	2500 - 8500 min ⁻¹
maximum cutting depth	25 mm
maximum disc Ø	115 mm

Battery voltage	18 V
Manufacturer's designation	CCG 18-115-10AS
Restart block	yes
Packaging	Modular case (L-Boxx)
Type of rechargeable battery	Lithium-ion
Weight	2.7 kg
Power supply	Mains operated
maximum vibration to EN	5 m/s ²
suitable battery - supplier / battery type / voltage	Bosch 18 V
Number of rechargeable batteries contained	0
Type of product	Angle grinder