



Compact angle grinder, Type: 72226760



Order data

Order number	077111 72226760
GTIN	4014586895802
Item class	03F

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Dust-resistant, powerful, low-maintenance and durable compact angle grinder with **brushless FEIN PowerDrive motor.**

Comprehensive user protection through:

- **Soft start**
- **Restart inhibit**
- **Blocking monitoring**
- **Electronic overload protection**
- **Speed pre-selection**
- **Recoil monitoring, anti-vibration handle and brake**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

Restart block	yes
Manufacturer's designation	CG 15-125 BL
Weight	2.2 kg
Special features	Brushless motor
maximum speed	3500 - 9000 min ⁻¹
maximum disc Ø	125 mm
maximum cutting depth	35 mm
Power consumption	1500 W
Type of product	Angle grinder