



Angle grinder Cordless, Type: 71220561



Order data

Order number	077149 71220561
GTIN	4014586896991
Item class	03F

Description

Version:

Fein 18V cordless angle grinder with AMPShare battery technology, for effective cutting, grinding and deburring work in assembly applications.

- **The new FEIN Power Drive motor, which is decoupled from the housing, ensures smooth running and low-vibration operation.**

Fein Protago safety angle grinder with a unique operating concept.

- **Safe guidance and two-hand operation by means of an additional handle with contact switch that can be adjusted in 6 positions and cannot be dismantled.**
- **Completely enclosed motor housing protects the motor from aggressive dust.**

Supplied with:

Without batteries and without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867

Technical description

Kick-back stop	yes
Weight	1.95 kg

Type of rechargeable battery	Lithium-ion
Restart block	yes
Soft start	yes
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
maximum disc Ø	125 mm
Power supply	Mains operated
Dead man's circuit	yes
Series	Protago
Packaging	Modular case (L-Boxx)
Manufacturer's designation	CCG18-125-10PD-SEC AS
Overload protection	yes
Number of rechargeable batteries contained	0
Type of product	Angle grinder