



Angle grinder Cordless, Type: 71220261



Order data

Order number	077149 71220261
GTIN	4014586898162
Item class	03F

Description

Version:

Fein 18V cordless angle grinder with AMPShare battery technology, for effective cutting, grinding and deburring work in assembly applications.

- **The new FEIN Power Drive motor, which is decoupled from the housing, ensures smooth running and low-vibration operation.**

Supplied with:

Without batteries and without charger. Supplied with protective hood, tool-less quick-clamping nut, anti-vibration handle, wrench, L-BOXX.

Note:

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867

Technical description

Type of rechargeable battery	Lithium-ion
Weight	2 kg
maximum disc Ø	125 mm
Restart block	yes
suitable battery - supplier / battery type / voltage	Bosch 18 V

Manufacturer's designation	CCG18-125-10 AS
Overload protection	yes
Kick-back stop	no
Soft start	yes
Power supply	Mains operated
Dead man's circuit	no
Battery voltage	18 V
Packaging	Modular case (L-Boxx)
Number of rechargeable batteries contained	0
maximum speed	2500 - 8500 min ⁻¹
Type of product	Angle grinder