



Straight die grinder Cordless, Type: 71230661



Order data

Order number	077259 71230661
GTIN	4014586897172
Item class	03F

Description

Version:

- **Dust-resistant and powerful cordless straight die grinder.**
- **Maintenance-free brushless EC motor with innovative cooling ribs for optimum cooling, including temperature monitoring.**
- **Ideal for every application. Optimum speeds, tailored to a large number of abrasives and materials thanks to stepless, electronic speed pre-selection.**

Long spindle neck. The long, slim neck makes deep plunging into workpieces possible (for example, internal grinding of pipes).

Supplied with:

Supplied with 6 mm Ø collet, 1 pc. 13 AF and 1 pc. 17 AF spanner, carrying case. **Without battery and charger.**

Note:

Straight die grinders are approved for use with burs up to a Ø of 12 mm.

Suitable batteries can be found under No. 073856 – 073858 or starter set under No. 073863 – 073867.

Technical description

maximum collet Ø	8 mm
Battery voltage	18 V
Number of rechargeable batteries contained	0

Manufacturer's designation	AGSZ 18-90 LBL AS
Speed range	2900 - 9000 min ⁻¹
Power supply	Rechargeable battery-powered
maximum vibration to EN	< 2.5 m/s ²
Weight	1.6 kg
electronic speed pre-selection	yes
suitable battery - supplier / battery type / voltage	Bosch 18 V
Packaging	Modular case (L-Boxx)
Type of product	Straight die grinder