



## Cordless sheet metal slitters / shears, Type: 71300661



### Order data

Order number	078103 71300661
GTIN	4014586898605
Item class	03F

### Description

#### Version:

**Cordless sheet metal shears** for mobile use.

#### Aviation snips.

- **Cuts well round curves with only minor sheet metal deformation.**
- **Comfortable and quick for seaming and cutting to length.**
- **For sheet metal up to 800 N/mm<sup>2</sup> and stainless steels.**
- **Four-way changeover blade: cleaner, burr-free cutting with low operating costs.**

#### Supplied with:

Including L-BOXX, **without** battery and **without** charger.

#### Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

### Technical description

maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.6 mm
Weight	2 kg
Radius of the smallest curve	15 mm

suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
Power supply	Rechargeable battery-powered
maximum vibration to EN	<2.5 m/s <sup>2</sup>
Battery voltage	18 V
Cutting speed	5 - 8 m/min
Rate of strokes	4000 min <sup>-1</sup>
Manufacturer's designation	ABLS 18 1.6 E AS
Cutting width	0 mm
maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	1 mm
Type of product	Aviation snips