



## Cordless beveller handheld, Type: AKFH18-5AS



### Order data

Order number	078123 AKFH18-5AS
GTIN	4014586898209
Item class	03F

### Description

#### Version:

For producing chamfers and radii on flat materials, sheet metal and containers, internal and external edges, contour profiles and for rounding off holes.

Powerful cordless beveller for optimum preparation of coatings for flexible working in the workshop and on the construction site. Cordless beveller up to 5 mm.

#### Supplied with:

**Without battery and charger**, 1 machine incl. 45° milling head (without guide roller, without indexable inserts), 3 clamping screws, 1 copper paste, 1 hexagon L-wrench 4 mm, 1 Torx screwdriver TX 15, 1 plastic tool case.

#### Note:

The necessary accessories can be found in our eShop from No. 078136 – 078138.

Suitable batteries can be found under No. 073851 – 073859 or starter set under No. 073863 – 073867.

### Technical description

Manufacturer's designation	AKFH 18-5 AS
Chamfer angle	45 degrees
No load speed	2400 - 7500 min <sup>-1</sup>

Radius	2.5 mm
Number of rechargeable batteries contained	0
Power supply	Mains operated
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Support table Ø	98 mm
Max. chamfer height 45°	5
suitable battery - supplier / battery type / voltage	Bosch 18 V
Packaging	Carrying case
Type of product	Deburring and chamfering machine