



## Cordless sheet metal slitters / shears, Type: 71300561



### Order data

Order number	078103 71300561
GTIN	4014586898599
Item class	03F

### Description

#### Version:

**Cordless sheet metal slitter** for mobile use.

#### Sheet metal slitter.

- **Distortion-free cut.**
- **Open cutting head for best view on to the cut**
- **QuickIN quick-change system for quick blade changing without tools or adjustment**

#### Supplied with:

Including L-BOXX, **without** battery and **without** charger.

#### Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

### Technical description

Packaging	Modular case (L-Boxx)
maximum vibration to EN	<2.5 m/s <sup>2</sup>
Number of rechargeable batteries contained	0
Weight	1.9 kg
maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	0.8 mm

Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Bosch 18 V
Manufacturer's designation	ABSS 18 1.6 E AS
Type of rechargeable battery	Lithium-ion
Radius of the smallest curve	90 mm
Cutting speed	5 - 8 m/min
maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.6 mm
Battery voltage	18 V
Cutting width	5 mm
Rate of strokes	3500 min <sup>-1</sup>
Type of product	Aviation snips