

Garant GRIDLINE

Support cabinet, for insert size length×width: 630X630mm**Order data**

| | |
|--------------|----------------|
| Order number | 431060 630X630 |
| GTIN | 4067263264958 |
| Item class | 41C |

Description**Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

Support cabinet, casing of sheet steel, with swing door (including storage shelf) and / or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL7035 light grey, front faces RAL 7016 anthracite.

Fitted with:

Door usable height: 345 mm

Number of shelves: 1

Number of cabinet casings with door: 1

Number of cabinet casings with drawers: 0

Note:

For vibration-absorbing machine mounts, please order 4 pcs. No. 086002 size 850.

Technical description

| | |
|-----------------------|--------|
| Door usable height | 345 mm |
| Support cabinet width | 606 mm |

| | |
|--|----------------|
| Support cabinet depth | 600 mm |
| Load capacity, distributed | 500 kg |
| Support cabinet height | 710 mm |
| Height of support cabinet incl. bearing sets | 770 mm |
| Number of shelves | 1 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Height adjustment | 25 mm |
| Hoffmann perforated panel grid interval | 9×9 |
| Cylinder lock | modular barrel |
| Type of product | Sub-frame |