

Grinding and inspection vice with threaded spindle, Jaw width A: 120mm



Order data

Order number	363250 120
GTIN	4067263239581
Item class	32K

Description

Version:

Ground Vee grooves.

All-steel, through hardened and **precision ground all round** for 4-face machining.

With threaded spindle. With horizontal Vee groove.

Application:

For **machining and inspection true to gauge.**

Accuracy:

Within **0.005 mm** / 100 mm.

Supplied with:

Sturdy **case.**

Technical description

Weight	13.9 kg
Jaw height C	40 mm
Overall length a	255 mm
Jaw width A	120 mm
maximum clamping range b	140 mm
Base body height G	55 mm
Overall width B	120 mm
Type of product	Checking vice

