



One-hand clamp, reversible, with rotating handle, Jaw capacity: 600mm



Order data

Order number	860288 600
GTIN	4008158042015
Item class	83K

Description

Version:

Upper and lower part of glass-fibre reinforced polyamide. Hollow profile rail made of burnished steel. The plastic housing protects the grip mechanism from dust and chips. The handle can be positioned in such a way that an optimal pumping position and thus better force application is achieved. The handle can also be swivelled out of the working area after the clamping process. This allows the use of several clamps in a very small space.

- **2-component plastic handle with pump lever.**
- **Innovative 360° rotating mechanism allows the grip unit to be placed around the rail.**
- **12-step detent mechanism to securely hold the grip position.**
- **Large clamping faces with removable protective caps.**
- **Clamping force of up to 1400 N.**
- **Tool-free changeover from clamping to spreading.**
- **One-handed operation without effort.**

Technical description

Jaw capacity	600 mm
Cross section of the slide rail	18×5 mm

maximum clamping force	1400 Nm
Manufacturer's designation	EZ360
Throat	80 mm
Spreading width	195 - 765 mm
Weight	1.06 kg
Type of product	Clamp