



MultiMaster MM 700 Max, Type: 72296863



Order data

Order number	077804 72296863
GTIN	4014586897868
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

Supplied with:

1× E-Cut universal saw blade (44 mm), L-BOXX.

Technical description

Toolholder	StarlockMax
Power consumption	450 W

Power supply	Mains-powered
Manufacturer's designation	MM 700 MAX
Amplitude (oscillation movement)	2 × 2.0 °
Weight	1.6 kg
Speed of oscillation	10000 - 19500 min ⁻¹
Cable length	5 m
Packaging	Modular case (L-Boxx)
Type of product	Oscillator