

# AEG

## Cordless angle grinder without rechargeable battery, Type: BEWS18BLPX



### Order data

Order number	077126 BEWS18BLPX
GTIN	4058546411428
Item class	07A

### Description

#### Version:

Brushless and high-performance 18 V angle grinder in a compact design.

- **Quick adjustment of the safety guard.**
- **Paddle switch for greater control and safety.**
- **LED warning lamp for protection against overloading.**

#### Supplied with:

Without battery and charger.

#### Note:

See No. 073820 and No. 073846 for suitable spare batteries and chargers.

### Technical description

maximum cutting depth	26 mm
maximum vibration to EN	5.4 m/s <sup>2</sup>
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Restart block	yes
Overload protection	yes
Number of rechargeable batteries contained	0

maximum disc Ø	125 mm
Dead man's circuit	yes
Type of rechargeable battery	Lithium-ion
Soft start	no
Weight	2.16 kg
Manufacturer's designation	BEWS18-125BLPX2-0
Power supply	Mains operated
maximum speed	8500 min <sup>-1</sup>
Kick-back stop	no
Type of product	Angle grinder