

# AEG

## Angle grinder Cordless, Type: BEWS18BLPX



### Order data

Order number	077108 BEWS18BLPX
GTIN	4058546411411
Item class	07A

### Description

#### Version:

Brushless, high-performance 18V angle grinder in a compact design.

- **Paddle switch for greater safety and control.**
- **Protective hood can be adjusted without tools.**

#### Supplied with:

**Without battery, without charger.** With cardboard box.

#### Note:

See No. 073820 and No. 073846 - 073848 for suitable spare batteries and chargers. Starter sets can be found under No. 073841 and No. 073844.

### Technical description

maximum cutting depth	22 mm
maximum disc Ø	115 mm
Power supply	Mains operated
Packaging	Modular case (HD=Heavy Duty)
Weight	1.97 kg
Battery voltage	18 V
Speed range	8500 min <sup>-1</sup>

suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	BEWS18-115BLPX2
Restart block	yes
maximum vibration to EN	5.6 m/s <sup>2</sup>
Type of product	Angle grinder

---

## Accessories

Li-ion batterySHD Battery type AS18	073846 AS18
Battery charger Type BL1418	073841 BL1418