

Garant**Fleece abrasive star, Ø 38 mm, Grit equivalent: 180****Order data**

Order number	555917 180
GTIN	4067263290704
Item class	51E

Description**Version:**

Star-shaped abrasive fleece with thread mounting. Tear-resistant and sturdy fleece body, no fraying at cut edges. 3-layer.

Application:

For cleaning, deburring, and finishing at hard-to-access places such as **bores, internal threads, pipes, and recesses**. Use clamping pin No. 555920.

Technical description

Colour	red
Grit equivalent	180
Grit designation	medium
Iron, sulphur and chlorine constituents	< 0,1 %
Product name attribute	Ø 38 mm
recommended speed	7500 min ⁻¹

maximum speed	13000 min ⁻¹
Type of product	Flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		