



## Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 8mm



### Order data

Order number	614853 8
GTIN	4018754239139
Item class	63A

### Description

#### Version:

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

#### Material:

Chrome alloy steel, chrome-plated.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 614820

### Technical description

Spanner length L	144 mm
Jaw height $h_1$	4.7 mm
Ring thickness $h_2$	7.4 mm
Ring $\varnothing$ D	18 mm
Jaw width b	17 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner