



Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 22mm



Order data

Order number	614853 22
GTIN	4018754320196
Item class	63A

Description

Version:

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

Material:

Chrome alloy steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614820

Technical description

Jaw width b	46.5 mm
Jaw height h ₁	10 mm
Ring thickness h ₂	13.5 mm
Spanner length L	285 mm
Ring Ø D	41 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner