



## Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 12mm



### Order data

Order number	614853 12
GTIN	4018754239177
Item class	63A

### Description

**Version:**

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

**Material:**

Chrome alloy steel, chrome-plated.

**Note:**

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 614820

### Technical description

Ring thickness $h_2$	8.4 mm
Spanner length L	173 mm
Jaw height $h_1$	6.4 mm
Ring $\varnothing$ D	23.5 mm
Jaw width b	25.2 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner