

**Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 17mm****Order data**

Order number	614853 17
GTIN	4018754239221
Item class	63A

Description**Version:**

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

Material:

Chrome alloy steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614820

Technical description

Ring Ø D	30.5 mm
Jaw width b	36.3 mm
Jaw height h ₁	7.9 mm
Spanner length L	229 mm
Ring thickness h ₂	10 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner