



Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 15mm



Order data

Order number	614853 15
GTIN	4018754239207
Item class	63A

Description

Version:

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

Material:

Chrome alloy steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614820

Technical description

Spanner length L	202 mm
Ring thickness h ₂	8.4 mm
Jaw width b	31.3 mm
Ring Ø D	28 mm
Jaw height h ₁	7.5 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner