



Open ended spanner / ratchet ring spanner reversible, 15° offset, Width across flats: 18mm



Order data

Order number	614853 18
GTIN	4018754239238
Item class	63A

Description

Version:

Drop forged. The integrated 72-tooth ratchet allows a working angle of just 5° – for efficient working even in confined spaces.

Material:

Chrome alloy steel, chrome-plated.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 614820

Technical description

Jaw height h_1	8.4 mm
Spanner length L	240 mm
Ring thickness h_2	11.5 mm
Ring \varnothing D	32 mm
Jaw width b	38 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated

End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	yes
Type of product	Spanner