



Pneumatic impact wrench Short version, Type: 9012M-1



Order data

Order number	079191 9012M-1
GTIN	4000896218356
Item class	03R

Description

Version:

Ultra-compact impact wrench with jumbo hammer impact mechanism, one-handed Changeover and **three-stage clockwise rotation**. 1200 Nm maximum release torque.

Technical description

Connection thread	NPT
Weight	1.27 kg
Length	80 mm
maximum air consumption	127.4 l/min
maximum vibration to EN	13.49 m/s ²
Tool arbor drive profile	Square
Tool arbor size	1/2 in
recommended hose size (internal Ø)	10 mm

Maximum screw \varnothing (8.8 - 12.9)	M20
Compressed air connection	1/4 in
maximum torque	678 N·m
Operating noise	92.2 dB(A)
maximum speed	8800 min ⁻¹
Type of product	Screwdriver