

**Garant****ESD table trolley T5, Type: T54****Order data**

Order number	971930 T54
GTIN	4067263515609
Item class	9GD

**Description****Version:**

Table trolley ESD conductive with **2 platforms**. Welded steel construction, platform made of volume conductive chipboard shelf with light grey, ESD-conductive surface. ESD-conductive Haptoprene® handle with impact-resistant polypropylene. **Electrically conductive wheels:** 2 fixed wheels and 2 castors (with brakes) with treadless TPE tyres, roller bearings, with fibre shields.

**Application:**

Suitable for use in EPAs with a conductive floor covering. The grounding is provided via the wheels; a separate grounding connection is not necessary. All plastic parts are conductive to prevent surface charging.

**Standard:**

DIN EN 61340-5-1

**Colour:**

Similar to RAL 7035 light grey **ESD powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Wheel Ø	125 mm
Depth	509 mm
Weight	34 kg
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Height of top shelf	850 mm
Material of wheel	TPE
Platform area depth	500 mm
maximum load capacity	250 kg
Height of bottom shelf	195 mm
Load capacity of top shelf	80 kg
Platform area width	850 mm
Height	1020 mm
Width	980 mm
electrostatic characteristic	EGB/ESD
Type of product	Table trolleys