

Garant**ESD Eurobox trolley with handle, Type: TNB1****Order data**

Order number	971950 TNB1
GTIN	4067263515616
Item class	9GD

Description**Version:**

ESD conductive Eurobox trolley with handle. Welded steel construction. ESD-conductive Haptoprene® handle with impact-resistant polypropylene. **Electrically conductive wheels:** 2 fixed wheels and 2 castors (with brakes) with treadless TPE tyres, roller bearings, with fibre shields. Suitable Euroboxes No. 972350 size ENB15 – ENB80.

Application:

Suitable for use in EPAs with a conductive floor covering. The grounding is provided via the wheels; a separate grounding connection is not necessary. All plastic parts are conductive to prevent surface charging.

Standard:

DIN EN 61340-5-1

Colour:

Similar to RAL 7035 light grey **ESD powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height	910 mm
Weight	9.6 kg
Wheel Ø	125 mm
Depth	400 mm
Number of castors with parking brake	2
Width	790 mm
Material of wheel	TPE
Number of fixed wheels without parking brake	2
Height of the mounting frame	180 mm
maximum load capacity	250 kg
electrostatic characteristic	EGB/ESD
Type of product	Trolley with handle