


Thread Core hole "Go" / "No Go" plug gauge 6H, Thread: M3



Order data

Order number	486055 M3
GTIN	2050002073661
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Design to DIN 2279 – 2299.

Design in accordance with DIN 2245.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Standard	DIN 13
Tolerance class	6H
Thread	M3
Thread type	M
Quality	6
Type of gauge	"No Go" gauge
Thread pitch	0.5 mm
Tolerance zone	H
Calibration	L6

Type of product

Thread NoGo plug gauge

ServicesCalibration "Go" / "No Go" plug gauge maximum \varnothing 20 mm

028300 20

DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm

028340 60