

Thread Core hole "Go" / "No Go" plug gauge 6H, Thread: M12



Order data

Order number	486055 M12
GTIN	2050002073821
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Design to DIN 2279 – 2299.

Design in accordance with DIN 2245.

Application:

For metric ISO threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Tolerance zone	H
Thread	M12
Quality	6
Type of gauge	"No Go" gauge
Standard	DIN 13
Thread type	M
Thread pitch	1.75 mm
Tolerance class	6H
Calibration	L6

Type of product

Thread NoGo plug gauge

ServicesCalibration "Go" / "No Go" plug gauge maximum \varnothing 20 mm

028300 20

DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm

028340 60