

## Thread Core hole "Go" / "No Go" plug gauge 6H, Thread: M4



### Order data

Order number	486055 M4
GTIN	2050002073678
Item class	48B

### Description

**Version:**

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Design to DIN 2279 – 2299.

Design in accordance with DIN 2245.

**Application:**

For metric ISO threads, right-hand DIN 13.

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

### Technical description

Standard	DIN 13
Quality	6
Type of gauge	"No Go" gauge
Tolerance zone	H
Thread	M4
Tolerance class	6H
Thread pitch	0.7 mm
Thread type	M
Calibration	L6

Type of product

Thread NoGo plug gauge

**Services**Calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  20 mm

028300 20

DAkkS calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  60 mm

028340 60