

**Carbide masonry drill, Drill Ø: 11 mm****Order data**

Order number	786001 11
GTIN	4058546404307
Item class	76G

**Description****Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

**Application:**

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

**Technical description**

overall length	150 mm
Drill Ø	11 mm
Flute length	90 mm
Shank Ø	11 mm

Tool material	Carbide
Standard	DIN 8039
Standard	ISO 5468
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill