

**Carbide masonry drill, Drill Ø: 5,5mm****Order data**

Order number	786001 5,5
GTIN	4058546404130
Item class	76G

Description**Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

Hammer and rotary bits with strong carbide cutter tip.

Application:

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

Technical description

Flute length	60 mm
Drill Ø	5.5 mm
overall length	100 mm
Shank Ø	5.5 mm

Tool material	Carbide
Standard	DIN 8039
Standard	ISO 5468
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill