

**Carbide masonry drill, Drill Ø: 10mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 786001 10     |
| GTIN         | 4058546404260 |
| Item class   | 76G           |

**Description****Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

**Application:**

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

**Technical description**

|                |        |
|----------------|--------|
| Drill Ø        | 10 mm  |
| overall length | 110 mm |
| Shank Ø        | 10 mm  |
| Flute length   | 60 mm  |

|                                  |                 |
|----------------------------------|-----------------|
| Tool material                    | Carbide         |
| Standard                         | DIN 8039        |
| Standard                         | ISO 5468        |
| Use with impact / without impact | Impact drilling |
| Shank                            | Plain shank     |
| Type of product                  | Masonry drill   |