



## Carbide masonry drill, Drill Ø: 20mm



### Order data

Order number	786001 20
GTIN	4058546404413
Item class	76G

### Description

#### Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip. With stepped shank with 3 drive flats.

#### Application:

Primarily for **drilling fastening holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

### Technical description

overall length	160 mm
Flute length	95 mm
Drill Ø	20 mm
Shank Ø	12.75 mm
Tool material	Carbide
Standard	DIN 8039
Standard	ISO 5468
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill

