

KÄRCHER**Industrial vacuum cleaner, Manufacturer's designation: IVR-L65/20****Order data**

Order number	078522 IVR-L65/20
GTIN	4054278695129
Item class	07D

Description**Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

2-motor 2.4 kW industrial vacuum cleaner with **tilting mobility trolley** and **65 litre tank**.

Supplied with:

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

Note:

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

Technical description

On/Off switch	yes
Vacuum	220 mbar

Operating noise	70 dB(A)
Width	570 mm
Power supply	Mains operated
Dust class – vacuum cleaner	L
Height	1330 mm
Container volume	65 l
Length	730 mm
Connection width	DN50 mm
Number of turbines	2
Weight	43 kg
Power consumption	2000 W
Air flow volume	100 l/s
Cable length	6 m
Type of product	Wet and dry vacuum cleaners