

Garant**Fleece compact disc, Ø 125 mm, Grit equivalent: 180****Order data**

Order number	567006 180
GTIN	4067263723721
Item class	51M

Description**Version:**

Crimped-in fibrous fleece with resin-bonded aluminium oxide grit permits **metal removal and finishing in a single operation. Universal disc** for light deburring work, for polishing out slight scratches and removing colouration.

Application:

For surface and edge grinding on angle grinders (recommended speed 6000 rpm).

Technical description

Version	3 S fine
Bore Ø	22.23 mm
Grinding medium code	SiC
Grinding media	Silicon carbide (SiC)
Degree of hardness	soft
Grit equivalent	180
Grit designation	fine
Iron, sulphur and chlorine constituents	< 0,1 %

Shape description	flat
Product name attribute	Ø 125 mm
optimised for material	Stone
optimised for material	Stainless steel
maximum circumferential speed	60 m/s
Type of product	Compact disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		