

**Garant**
**Workshop set, Number of tools: 23**

**Order data**

Order number	955002 23
GTIN	4067263723691
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

**Suitable for:**

**GARANT roller cabinets** with full extension drawers and a drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Roller cabinets No. 914520 – 914582.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 955002

: 1 pc.

GARANT IP54 digital caliper No. 412680 size 150: 1 pc.

GARANT tape measure No. 462210 size 3: 1 pc.

GARANT light metal spirit level No. 467020 size 250: 1 pc.

GARANT combination spanner No. 613600 size 5.5; 7; 8; 10; 13; 16; 17; 18; 19: 1 pc. each

GARANT screwdriver for slot-head No. 660032 size 3.5; 5.5; 6.5: 1 pc. each

GARANT screwdriver for Phillips No. 667702 size 1; 2; 3: 1 pc. each

GARANT combination pliers No. 700940 size 180: 1 pc.

GARANT water pump pliers No. 706001 size 250: 1 pc.

GARANT snipe-nose pliers No. 713040 size 200: 1 pc.

GARANT side cutter No. 724840 size 160: 1 pc.

GARANT general-purpose knife with 2-component handle with 3 blades No. 845020: 1 pc.

## Technical description

Drawer usable area in G	20×16
Width	500 mm
Number of tools	23
Depth in G	16
Version	for roller cabinet drawer
Width in G	20
Depth	400 mm
Power supply	Battery-powered
Rigid foam quality LD45, thickness	30 mm
suitable for workstations and storage equipment	Roller cabinet
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

## Accessories

Rigid foam inlay for tool sets suitable for rigid foam set 955002	952001 955002
Digital caliper IP54 with data output Measuring range 150 mm	412680 150
Tape measure with viewing window Band length 3 m	462210 3
Light metal spirit level Length 250 mm	467020 250
Combination spanner Width across flats 10 mm	613600 10
Combination spanner Width across flats 13 mm	613600 13
Combination spanner Width across flats 16 mm	613600 16
Combination spanner Width across flats 17 mm	613600 17
Combination spanner Width across flats 18 mm	613600 18

Combination spanner Width across flats 19 mm	613600 19
Combination spanner Width across flats 5,5 mm	613600 5,5
Combination spanner Width across flats 7 mm	613600 7
Combination spanner Width across flats 8 mm	613600 8
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 3,5 mm	660032 3,5
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660032 5,5
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 6,5 mm	660032 6,5
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667702 1
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667702 2
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 3	667702 3
Combination pliers, chrome-plated, with 2-component grips overall length 180 mm	700940 180
Water pump pliers with stepped fine adjustment, black overall length 250 mm	706001 250
Snipe nose pliers, straight, chrome-plated, with grips overall length 200 mm	713040 200
Diagonal side cutter chrome-plated, with grips overall length 160 mm	724840 160
General-purpose knife with 2-component handlewith 3 blades, 18 mm	845020