

Garant

Electrically height-adjustable workstation (2 lift columns) Load capacity max. 500 kg, Type: 2000

**Order data**

Order number	920312 2000
GTIN	4067263736219
Item class	91S

Description**Version:**

Base frame with anodised aluminium lift unit. With cross bracing for stabilisation. 50 mm thick worktop made of beech marine ply. Stepless height adjustment from 740 – 1140 mm, quickly and easily selected using the control panel. Control panel with memory function for 3 different working heights.

Supplied with:

4 floor levelling screws.

Colour:

Base frame with aluminium lift unit and steel hollow section RAL 7016 anthracite **powder-coated**.

Recommendation:

Ergonomic working for seated and standing tasks!

Note:

Only cabinet bodies up to maximum 500 mm height can be installed under the worktop.

Technical description

maximum load capacity	500 kg
Worktop length	2000 mm

Principle of height adjustment	complete structure
Width	2000 mm
Stepless height adjustment	yes
Depth	750 mm
Worktop thickness	50 mm
Supply voltage	250 V
Height adjustment range (worktop surface) from – to	740 - 1140 mm
Power supply	Mains operated
Worktop depth	750 mm
Surface worktop	clear varnished
Weight	88 kg
Plug type, input	F
Material of worktop	Beech marine ply
Continuous load capacity	350 kg
Workbench/desk load capacity - maximum distributed load (on wood)	500 kg
Type of height adjustment	electric
Insert thickness	50 mm
Height adjustment	25 mm
Type of product	Workbench