

RUNPOTEC
HAUPTKABELNENZIEHSPEZIALIST

GF3 fibreglass cable pulling rod in a plastic box With integrated digital meter counter, Band length: 30m



Order data

Order number	814869 30
GTIN	9120045477122
Item class	86A

Description

Version:

3 mm thick fibreglass rod **accepts pushing force** yet is **highly flexible**; ideal for pulling cables into complicated runs where conduit is already laid or where there are many bends in the conduit.

Ergonomic holding and carrying handle. Patented guiding head with anti-twist and kink protection (2 pcs. external thread Ø RTG 6 mm). Automatic glide back protection. Anti-slip coating. Suitable for construction sites, splash-proof and dust-proof, shock-proof and break-proof. Possible up to a radius of 38 mm.

Also compatible with RUNPOCAM RC2 (No. 814878) and the basalt rods (No. 814877).

With integrated digital meter counter.

Supplied with:

Accessories securely stored in a plastic box: 1 flexible guiding head (RUNPOGLIDE) with anti-twist protection, 1 anti-kink end sleeve RTG Ø 6 mm, 1 pull-in aid, 1 special adhesive 3 g, 1 cable pull loop (Ø 14 mm external), 6 adhesive sleeves Ø 3 mm, 3 pull eyes Ø 7 mm, 1 starting bulb Ø 11 mm, 1 connecting sleeve, 2 mounting wrenches, 1 CR2032 button battery.

Technical description

Band length	30 m
Maximum load on connection between cable pulling rod and sleeve	1.3 kN
Maximum load on cable pulling rod	4.5 kN
Type of product	Cable pulling tool