



## Snipe-nose combination pliers chrome-plated, with grips145



### Order data

Order number	701651 145
GTIN	
Item class	73F

### Description

#### Version:

Gripping faces with special three-point contour for secure gripping of flat parts. Easy cutting thanks to high ratio compound action. Milled slot in the gripping area enables small workpieces such as nails, pins and bolts to be held and pulled. Handy for working in inaccessible locations. Slim head profile with tapered jaws.

Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface. KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

#### Standard:

**DIN ISO 5746.**

#### Material:

Special tool steel.

#### Note:

Previous model No. 701650 can still be ordered until the KNIPEXtend models are available.

### Technical description

Cutting capacity hard wire up to Ø	2 mm
overall length	145 mm
Cutting capability medium hard wire up to Ø	3 mm
Handle	Multi-component covering
Material	Special tool steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers